

## DIRECT-TO-DRAIN SYSTEM



### Kiss your condensate tanks goodbye.

The steam and condensation produced by your steriliser can be time-consuming and messy to empty from condensate tanks. It can even melt plumbing if not cooled sufficiently before pouring down the drain.

Finally, a product designed to provide a reliable and efficient solution. The VistaCool™ direct-to-drain system is designed to reduce the temperature of steriliser wastewater – eliminating condensate bottles and tanks! Also, using VistaCool™ with larger chamber sterilisers can reduce maintenance by allowing you to use fresh distilled water with every cycle.



#### Single Unit

Designed to be compatible with Midmark and other bechtol steriliser models  
Part No. 9A586001



#### Double Unit

Designed to be compatible with any two current Midmark sterilizers and other benchtop steriliser models  
Part No. 9A586002

### Protects Staff

- Eliminates hazardous handling of hot condensate tanks
- Can reduce steriliser maintenance – saving time and effort

### Protects Drains

- Designed to prevent steriliser wastewater from melting plumbing
- Built-in backflow prevention meets or exceeds local plumbing codes

### Protects Cabinets

- Helps prevent mold and mildew caused by spills and exhaust from condensate tanks
- Helps protect cabinets from rot and rust by sending cooled wastewater directly and safely to the drain

#### Designed to be compatible with:

Midmark M3 UltraFast® Automatic Steriliser  
Midmark M9 & M11 UltraClave® Automatic Sterilisers\*  
Midmark Newmed sterilisers  
Statim 2000, Statim 5000  
and some other leading steriliser brands

\*Required adapter kit included. Compatible with the double unit only.

VistaCool™




# VistaCool™ is more than a product, it's a solution.

Eliminating the need to manually empty condensate tanks, VistaCool™ will allow you and your staff to spend more time chair side and less time tending to office equipment. This safe and reliable solution is designed to enhance office efficiency. Less work for staff means more time to care for patients.

## Specifications

	Single	Double
Tank material:	Polyethylene – Natural White	Polyethylene – Natural White
Tank dimensions w/fittings:	7.6" W x 7.6" L x 13.75" H (19.3 cm x 19.3 cm x 34.9 cm)	4.0" W x 13.0" L x 17.0" H (10.2 cm x 33.1 cm x 43.2 cm)
Tank volume:	1.50 gal (5.70 liters)	3.00 gal (11.40 liters)
Tank weight w/water & fittings:	15.0 lb (6.8 kg)	28.0 lb (12.7 kg)
Approximate shipping weight:	7.0 lb (3.2 kg)	10.0 lb (4.5 kg)
Coolant water connection:	Supply fitting for ¼" O.D. required. To be provided by installer.	Supply fitting for ¼" O.D. required. To be provided by installer.
Max coolant water pressure:	100 psi (6.9 bar)	100 psi (6.9 bar)
Max altitude (If using air gap):	6,561 ft (2,000 m)	6,561 ft (2,000 m)



For more information

Distributed by:

**ICONA**

DESIGNED WITH YOU IN MIND

Unit 9 25-41 Redwood Drive  
Dingley Victoria 3172

T 1300 442 662  
W www.icona.net.au

**VistaCool™**

**MIDMARK®**

Because we care.